

# Vertical I-Line Panel

UP TO 3000A

**PART NUMBER: IL-306-LDE**

**PRODUCT DESCRIPTION:**

3000A Trystar Vertical I-Line Panel

I-Line Interior Rated for 600V

UL 50 Listed

NEMA 3R

65 kAIC Rated when using 65kAIC Rated Breakers

**INPUT:**

8 Sets of Male 16 Series Panel Mounts (BK, RD, BE, WT, GN)

Hardwire Access through Bottom Conduit Trap Door

**OUTPUT:**

Female 16 Series Panel Mounts

Hardwire Access through Bottom Conduit Trap Door

**STANDARD FEATURES:**

I-Line Interior Includes 1 x 63" Sections of Breaker Space on

Left Side of Panel and 2 x 22.5" Sections on the Right Side

All Aluminum Corrosion Resistant Construction

Changeable Gland Plates Make the Trystar I-Line Adaptable

Heavy Duty Cage with Lifting Eyes and Forklift Pockets

Metal Casters with Industrial Grade Floor Locks

Protective Caps on all Panel Mounts to Prevent Accidental Contact

Powder Coat Color: Customer Choice

UV Print: Customer Logo

Made in the USA

**BREAKER SPACE:**

108" I-Line Interior Available:

150A Adjustable Breaker Range: 150A to 50A (4.5" space)

250A Adjustable Breaker Range: 250A to 70A (4.5" space)

400A Adjustable Breaker Range: 400A to 125A (6" space)

**\*MULTIPLE CONFIGURATIONS: CONTACT TRYSTAR FOR MORE INFORMATION**

